

# Oasis 3-Piece, 60-inch, Ramped Threshold, Roll-In Shower Compartment With ActivLife 3-Bar (2-horizontal / 1-vertical) And Folding Seat Package



**Specification** – Oasis 3-piece FRP gelcoat shower compartment SH3P-MD-6032, having a 1/2-inch high maximum finished threshold with floor attachment flange on lower threshold. ActivLife package includes a horizontal bar across the back wall and side wall opposite the seat, a vertical bar on the side wall opposite the seat, a folding seat, and shower curtain rod.

**Standards Certification:**

The shower compartment listed is manufactured in compliance with ANSI Z124 Standards, and certified through an ongoing, independent quality assurance and testing program.

The factory-applied grab bar and seat package is certified through an independent review program.

**NOTE:** This model DOES NOT meet the required interior dimensions for ADA Roll-In Shower compliance.




**SH3P-MD-6032 R / TLV-LS**  
(RH drain / LH seat / 3-bar package)  
Model & Package Illustrated

**NOTE:** Seat positioning prohibits the installation of a shower enclosure.



**Home Innovation**  
LAB CERTIFIED™



Dimensions shown are maximum. Due to the nature of the materials involved, actual unit dimensions can vary (tolerances: + / - 1/8 inch). Oasis reserves the right to modify or discontinue product and/or associated equipment without prior written or verbal notification or obligation.

| Model ID | Package Code | Description (define configuration referencing drain end) |
|----------|--------------|--|
|----------|--------------|--|

|   |  |  |
|---|--|--|
| SH3P-MD-6032 L (left drain) / TLV-RS (right seat)<br>SH3P-MD-6032 R (right drain)/ TLV-LS (left seat) |  | 60" x 32", 3-piece, end drain, ramped 1/2-inch threshold shower with ActivLife 1.50" dia. 3-bar and seat package (horizontal back & opposite seat wall bars, vertical bar opposite seat, and folding seat) and shower curtain rod. |
|---|--|--|

**Powder Coated Bar Packages (1.25-inch dia.)**

|   |  |  |
|---|--|--|
| SH3P-MD-6032 L (left drain) / TLV-RS WHT (right seat)<br>SH3P-MD-6032 R (right drain)/ TLV-LS WHT (left seat) |  | 60" x 32", 3-piece, end drain, ramped 1/2-inch threshold shower with ActivLife 1.25" dia. white powder coated 3-bar and seat package (horizontal back & opposite seat wall bars, vertical bar opposite seat, and folding seat) and shower curtain rod. |
|---|--|--|

|   |  |  |
|---|--|--|
| SH3P-MD-6032 L (left drain) / TLV-RS OFW (right seat)<br>SH3P-MD-6032 R (right drain)/ TLV-LS OFW (left seat) |  | 60" x 32", 3-piece, end drain, ramped 1/2-inch threshold shower with ActivLife 1.25" dia. off-white powder coated 3-bar and seat package (horizontal back & opposite seat wall bars, vertical bar opposite seat, and folding seat) and shower curtain rod. |
|---|--|--|

|   |  |  |
|---|--|--|
| SH3P-MD-6032 L (left drain) / TLV-RS SNK (right seat)<br>SH3P-MD-6032 R (right drain)/ TLV-LS SNK (left seat) |  | 60" x 32", 3-piece, end drain, ramped 1/2-inch threshold shower with ActivLife 1.25" dia. nickel finish 3-bar and seat package (horizontal back & opposite seat wall bars, vertical bar opposite seat, and folding seat) and shower curtain rod. |
|---|--|--|

DELETE / SHWR ROD-SH Delete shower curtain rod from package.

**Package Notes:**

1. Model available without listed package.
2. Model available without vertical bar on control side wall, see ActivLife "TL-RS/LS" package code.
3. For bar packages without seat, see ActivLife "BP1-60" and "BP2-60" package codes
4. For REINFORCEMENT ONLY replicating "TL" package with RH or LH seat reinforcement, see ActivLife "TLRF-RS" or "TLRF-LS" package code.
5. For REINFORCEMENT ONLY for horizontal bars (HUD/FHA-Fair Housing), see ActivLife "FH" package code.
6. For expanded reinforcement package options, (with or without listed package components), see ActivLife "3SM" and "3SF" package codes.






Photo 1: Grab Bars: Factory-installed 1.50-inch diameter, concealed attachment, 18 gauge, #304 brushed stainless steel grab bars. Concealed attachment design provides tamper-resistance and minimizes debris collection areas at contact points, compared to common exposed flange bar designs, without compromising bar attachment integrity. (Reinforced areas include a structural core material encapsulated in FRP composite.)

Photo 2: Grab Bars: Factory-installed 1.25-inch dia. powder coated (in finishes listed above), concealed attachment, 18 gauge, #304 stainless steel grab bars. Concealed attachment design provides tamper-resistance and minimizes debris collection areas at contact points, compared to common exposed flange bar designs, without compromising bar attachment integrity. (Reinforced areas include a structural core material encapsulated in FRP composite.)

Photo 3: Shower Bench Seat: Factory-installed shower bench seat with non-porous, high-pressure laminate upper and lower surfaces, fused to high-density phenolic core. The seat area secures to an 18 gauge, #304 stainless steel framework, and easily pivots upward to store along the wall without supplemental fasteners. Heavy-duty wall (hinge) bracket design eliminates supplemental legs and is formed from 10 gauge, #304 brushed stainless steel. (Reinforced area includes a structural core material encapsulated in FRP composite.)

Photo 4: Shower Curtain Rod: Factory-installed 1.00-inch diameter, concealed attachment, 18 gauge, stainless steel shower curtain rod with polished finished.