Oasis 42-inch Shower Compartment With ActivLife 2-Bar (2-horizontal) And Folding Seat Package



Specification – Oasis one-piece FRP gelcoat shower compartment SH-4234, offered in a standard 4-inch or 6-inch (ABF) dam configuration. ActivLife package includes a horizontal bar across the back wall and side wall opposite the seat, and a folding seat.

Standards Certification:


The shower compartment listed is manufactured in compliance with ANSI Z124 Standards, and certified through an ongoing, independent quality assurance and testing program.

The factory-applied grab bar and seat package are certified through an independent review program.




SH-4234 / TL-LS (LH seat / 2-bar package) Model & Package Illustrate

Model & Package Illustrated




NOTE: Positioning of factory attached grab bars and seat allow for installation of a shower enclosure.





Enclosure Size:

38-1/2"w (max) x 68"h (max)




Drain Clearance

Model ID	Package Code	Description (define configuration referencing seat side)
SH-4234 (Std or ABF) SH-4234 (Std or ABF)	/ TL-RS (right seat) / TL-LS (left seat)	42" x 34", center drain shower with 4" (std) or 6" (ABF) dam, and ActivLife 1.50" dia. stainless steel 2-bar and seat package (single horizontal back & opposite seat wall bars with folding seat).
Powder Coated Bar Packages (1.25-inch dia.)		
SH-4234 (Std or ABF) SH-4234 (Std or ABF)	/ TL-RS WHT (right seat) / TL-LS WHT (left seat)	42" x 34", center drain shower with 4" (std) or 6" (ABF) dam, and ActivLife 1.25" dia. white powder coated 2-bar and seat package (single horizontal back & opposite seat wall bars with folding seat).

Package Notes:

- 1. Model available without listed package.
- 2. Model available with vertical bar on control side wall, see ActivLife "TLV-RS/LS" package code.
- 3. Model available without seat, see ActivLife "BP1", "BP2", and "BP5" package codes.
- 4. For REINFORCEMENT ONLY for bars (HUD/FHA-Fair Housing), see ActivLife "FH" and "FHV" package codes.
- 5. For expanded reinforcement package options, (with or without listed package components), see ActivLife "3SM" and "3SF" package codes.









- Photo 1: Grab Bars: Factory-installed 1.50-inch diameter, concealed attachment, 18 gauge, #304 brushed stainless steel grab bars. Concealed attachment design provides tamper-resistance and minimizes debris collection areas at contact points, compared to common exposed flange bar designs, without compromising bar attachment integrity. (Reinforced areas include a structural core material encapsulated in FRP composite.)
- Photo 2: Grab Bars: Factory-installed 1.25-inch dia. powder coated (in finishes listed above), concealed attachment, 18 gauge, #304 stainless steel grab bars. Concealed attachment design provides tamper-resistance and minimizes debris collection areas at contact points, compared to common exposed flange bar designs, without compromising bar attachment integrity. (Reinforced areas include a structural core material encapsulated in FRP composite.)
- Photo 3: Shower Bench Seat: Factory-installed shower bench seat with non-porous, high-pressure laminate upper and lower surfaces, fused to high-density phenolic core. The seat area secures to an 18 gauge, #304 stainless steel framework, and easily pivots upward to store along the wall without supplemental fasteners. Heavy-duty wall (hinge) bracket design eliminates supplemental legs and is formed from 10 gauge, #304 brushed stainless steel. (Reinforced area includes a structural core material encapsulated in FRP composite.)